

UWTSD PRINTED TEXTILE WORKSHOP & DYE LAB NOTES

Technique

Printing with iron mordant.

Suitable fabrics and fibres

linen, cotton, silk, wool.

Method

Pre-made { 1000ml - 20gm }
90gms of guar gum thickener }
10gms iron.

Fixation

Air or heat drying.

Notes

Technique

Printing with Alum mordant

Suitable fabrics and fibres

linen, cotton, silk, wool.

Method

Pre-made { 1000ml - 20gm }
90gms of guar gum thickener.

90gms of guar gum added to 10gms Alum

Fixation

Air or heat drying.

Notes